



SPECIFICATIONS
Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard:PBT
Max.Processing Temp:180°C for 30-60 seconds
(200°C for 10 seconds)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-200D-065-B		版本 REV.	A
			.X±0.30	X.'±3°	审核 CHECK	LEO			品名 TITLE	2.00 Mini Jumper 1*2Pin Close Type		页次 SHEET	1/1
			.XX±0.20		核准 APPROVAL	JOHN			客户料号 CUTM.NO.				
			.XXX±0.10						兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.				
					单位 UNITS	MM	比例 SCALE	1:1					