





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to +85°
Contact Material: Brass
Standard: PBT
Contact Plating: Ni

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-254D-065-B		版本 REV.	A
			.X±0.30	X.°:±5°	审核 CHECK	LEO			品名 TITLE	2.54MINI JUMPER(6.4) Close		页次 SHEET	1/1
			.XX±0.25	X.X°:±1°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.				
			.XXX±0.20	X.XX°:±0.5°					单位 UNITS	MM	比例 SCALE		