






NOTE:

Technical data:
Insulator body:PBT+15% G.F UL94-V0
Curent Rating:3 AMP
Insulator resistance:1000 Megohms min
Dielectric withstanding:AC/DC 500V.
Contact Resistance:25mΩ
Contactmaterial:Bronze.
plating:Gold or tin over nickel
Operating Temperature:-40°C to +105°C

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-200D-060-B		版本 REV.	A
			.X±0.25	X.°±1°	审核 CHECK	EVA			品名 TITLE	MJ PH2.0 H:3.5		页次 SHEET	1/1
			.XX±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XXX±0.10		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				