






SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 500V
Operation Temperature: -40°to +85°
Contact Material: Brass
Standard: PBT
Contact Plating: Ni

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-254D-065-B		版本 REV.	A
			.X±0.30	X.°±1°	审核 CHECK	EVA			品名 TITLE	2.54mm 开口短路帽		页次 SHEET	1/1
			.XX±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XXX±0.10						Bossie (博锡)				
					单位 UNITS	MM	比例 SCALE	1:1					