




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: $1000M\Omega$ Min
Contact Resistance: $20m\Omega$ Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to $+85^{\circ}$
Contact Material: Brass
Standard: PBT
Contact Plating: Ni

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES				
DECIMALS:	ANGLES:	TITLE: 2.54MM MINI JUMPER (6.4) Close		
X.: ± 0.30	X.: $\pm 5^{\circ}$			
X.X: ± 0.25	X.X': $\pm 1^{\circ}$			
X.XX: ± 0.20	X.XX': $\pm 0.5^{\circ}$			
CUSTOMER COPY		SIZE: A4	SHEET: 1F1	REV: A