





REVISIONS					
#	LY#	DESCRIPTION	DATE	OWN	APVD
A		REVISED PER ECN-23-216128	09JUN2023	SK	DZ
A1		REVISED PER ECR-24-203079	13MAY2024	MV	CO




CIRCUIT POSITION NUMBER




TOOL CAVITY NUMBER


2443725-4 SHOWN




1*7 POSITION



1*8 POSITION




1*9 POSITION



1*10 POSITION

- 1. MATERIAL: THERMOPLASTIC, UL94V-0, COLOR: NATURAL
 - 2. APPLICABLE CONTACT P/N 2443728-1
 - 3. MATING CONNECTOR P/N PLUG HSG: 2443729-1 GANG SEAL: 2443732-1/2321922-1
 - 4. COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)
- NOTE DELETED.




1*2 POSITION

SCALE 2:1



1*6 POSITION

SCALE 2:1




1*3 POSITION

SCALE 2:1




1*7 POSITION

SCALE 2:1




1*4 POSITION

SCALE 2:1




1*8 POSITION

SCALE 2:1



1*5 POSITION

SCALE 2:1



1*9 POSITION

SCALE 2:1



1*10 POSITION

SCALE 2:1

DIM "E"	DIM "D"	DIM "C"	DIM "B"	DIM "A"	POSITION	PART NUMBER
26.07	22.50	1.25	29.50	29.38	1*10	1-2443725-0
26.07	20.00	0	27.00	26.88	1*9	2443725-9
26.07	17.50	1.25	24.50	24.38	1*8	2443725-8
26.07	15.00	0	22.00	21.88	1*7	2443725-7
23.07	12.50	1.25	17.90	17.40	1*6	2443725-6
23.07	10.00	0	15.40	14.90	1*5	2443725-5
23.07	7.50	1.25	12.90	12.40	1*4	2443725-4
23.07	5.00	0	10.40	9.90	1*3	2443725-3
23.07	2.50	1.25	7.90	7.40	1*2	2443725-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.25
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

MATERIAL: 1

OWN: SANTOSH K 12DEC2022
 CHK: OTTO CHECN 12DEC2022
 APVD: ZHANG DANIEL 12DEC2022

NAME: CAP HOUSING, FREE HANGING, SDL 2.5 WATERPROOF

SIZE: A1
 CAGE CODE: 00779
 DRAWING NO: 2443725

RESTRICTED TO: -

CUSTOMER DRAWING

SCALE: 4:1 SHEET 1 OF 1 REV A1