

	DIM. A	DIM. B
9P	40.64	45.72
8P	35.56	40.64
7P	30.48	35.56
6P	25.4	30.48
5P	20.32	25.4
4P	15.24	20.32
3P	10.16	15.24
2P	5.08	10.16
NUMBER OF PINS	DIM. A	DIM. B



适应基板厚度: 1.2mm~1.6mm
温度范围: -25℃~85℃
额定电压: 250V AC/DC
额定电流: 7A
接触电阻: $\leq 0.01\Omega$
绝缘电阻: $\geq 1000M\Omega$
耐压: 1500V AC/minute

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。



深圳市韩下电子有限公司

DRAW :	黄彬	2021-06-16	TITLE: 插件针座		DRAW NAME: HX-CH5.08-6PZZ		
DESIGN:							
CHECK:	张伟	2021-06-16	SERIES: 1501 SERIES		DRAW NO.		
APPROVED	罗小春	2021-06-16	P/N:		UNIT:	SHEET:	
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	mm	1/1	