





REVISION RECORD				
REV	ECO	DESCRIPTION	DRF	CHKD



PC Board Layout
Component Side Shown

Specifications:

1. Electrical:

Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state

Insulation resistance: 500MΩ Min

Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750 Cycles 20-30Cycles/Min

3. Material:


Housing: Glass Filled Polyester UL94V-0

Contact: Phosphor Bronze

Plating: Gold Plating 50u " Over Nickel

4. Temperature Range: -25°C to +85°C.

5. Welding temperature: 260±5°C 3±0.5S

DETAILS LIST			DFTO: 黄彬		DATE: 2017.05.03		 深圳市韩下电子有限公司			
	TOLERANCES EXCEPT AS NOTED		CHKD: 张伟		DATE: 2017.05.03					
			MFO:		DATE:					
			APPVL: 罗小睿		DATE: 2017.05.03					
							TITLE HX-RJ45 90 5621-1x1 10P8C S			
	ANGLES ± 0.5		QTY :							
			FINISH :							
							DRAWING NO. TES6A1001			
	THIRD ANGLE PROJECTION						/PART NO.			
							SIZE			
						REV				
						A3				
						0				
						DO NOT SCALE DRAWING				
						SHEET X OF Y				