





SECTION A-A

**Specifications:****1. Electrical:**

Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state
Insulation resistance: 500MΩ Min
Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750 Cycles 20-30Cycles/Min

3. Material:

Shell: Brass
Housing: LCP+15% G.F UL94V-0
Contact: Phosphor Bronze
Plating: Gold Plating 50u" Over Nickel
4. Temperature Range: -25°C to +85°C. 5. Welding
temperature: 260±5°C 3±0.5S

C	/	屏蔽壳	黄铜	镀镍	
B	/	PIN脚	磷铜	镀金	
A	/	底座	LCP	黑色	
序号	材料料号	品名	材质	电镀/颜色	备注

借(通)用件登记

旧底图总号

标记	处数	更改文件号	签字	日期
----	----	-------	----	----

视角



未注 X. ±0.30 X° . ±2°
明公 . X ±0.20 . X° . ±1°
差 . XX ±0.15 . XX° . ±0.5°
差 . XXX ±0.05 . XX° . ±0.5°

RJ45 网络插座(沉板全包)

底图总号

设计	黄彬	2020.8.25
审核	张伟	2020.8.25
工艺		

图样

标记 重量 比例

HX-RJ45 90 SMT8.6CB

共 1 页

第 1 页

签字 日期

标准化	
批准	罗小春 2020.8.25



深圳市韩下电子有限公司