







PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

- | | |
|--------------------|---|
| 1.HOUSING MATERIAL | :GLASS FILLED POLYESTER UL94V-0. |
| 2.CONTACT MATERIAL | :PHOSPHOR BRONZE $\phi 0.46\text{mm}$. |
| 3.PLATING | :GOLD PLATING OVER NICKEL. |
| 4.LED | :OPTION |

ELECTRICAL:

- | | |
|--------------------------------------|------------------------------|
| 1.VOLTAGE RATING | :125 VAC RMS. |
| 2.CURRENT RATING | :1.5 AMP. |
| 3.CONTACT RESISTANCE | :30 MILLIOHMS MAX. |
| 4.INSULATION RESISTANCE | :500 MEGOHMS MIN @ 500V DC . |
| 5.DIELECTRIC WITHSTANDING RESISTANCE | :1000V AC RMS 50Hz. 1MIN. |

MECHANICAL:

- | | |
|----------------------------|------------------|
| 1.DURRABILITY | :750 CYCLES MIN. |
| 2.PCB RETENTION PRE-SOLDER | :1 LB MIN. |

ENVIRONMENTAL:

- | | |
|--------------|---------------|
| 1. STORAGE | : -40°C~+85°C |
| 2. OPERATION | : -25°C~+85°C |

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 网口插座 RJ45-8P/8C 5JC-2*1 弯插 带屏蔽 带灯 带弹					
DRAWN: YYF	DATE: 2024-04-30	PROD. P/N		R-RJ45R08P-C202			
		UNIT	mm	SCALE	free		
		FILE NO.		Ckmtw-RJ45-0190		REV. A	HY04

TOLERANCE TABLE

.0	± 0.20
.00	± 0.10
.000	± 0.05