





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



PC Board Layout
Component Side Shown

Specifications:

1. Electrical:

Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state

Insulation resistance: 1000MΩ Min

Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750 Cycles 20-30Cycles/Min

3. Material:

Housing: Glass Filled Polyester UL94V-0

Contact: Phosphor Bronze

Plating: Gold Plating Fu "50u" Over Nickel

4. Temperature Range: -25°C to +85°C.

5. Welding temperature: 260±5°C 3±0.5S

MM (INCH) TOLERANCES EXCEPT AS NOTED MM .0 ± 0.15 .00 ± 0.075 .000 ± 0.05 ANGLES ± 0.5 THIRD ANGLE PROJECTION	DFTO 黄彬	DATE 2020.8.25	深圳市韩下电子有限公司 HANXIA TITLE HX-RJ45 90 5631-1x1 8P8C S	
	CHKD 张伟	DATE 2020.8.25		
	MFO	DATE		
	APPVL 罗小峰	DATE 2020.8.25		
	MATERIAL :		QT'Y :	
FINISH :		DRAWING NO.		SIZE A3
SCALE :		/PART NO.		REV 0
DO NOT SCALE DRAWING		SHEET X		OF Y