





REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



PC Board Layout
Component Side Shown

Specifications:

1. Electrical:

Rated voltage and current: 125V 1.5A Max
Contact resistance: 50mΩ Max Initial state
100mΩ Max End state

Insulation resistance: 500MΩ Min
Withstand Voltage: AC 1000V

2. Mechanical:

Durability: 750 Cycles 20-30Cycles/Min

3. Material:

Housing: Glass Filled Polyester UL94V-0

Contact: Phosphor Bronze

Plating: Gold Plating Fu "50u" Over Nickel

4. Temperature Range: -25°C to +85°C.

5. Welding temperature: 260±5°C 3±0.5S

DETACHED LISTS .8 ± 0.15 .80 ± 0.075 .800 ± 0.05 ANGLES ± 0.5 THIRD ANGLE PROJECTION	DFTO: 黄彬 DATE: 2020.8.25 CHKD: 张伟 DATE: 2020.8.25 MFO: DATE: APPVL: 罗小梅 DATE: 2020.8.25 MATERIAL: QTY: FINISH: SCALE:	深圳市韩下电子有限公司 HANXIA	
	TOLERANCES EXCEPT AS NOTED	TITLE HX-RJ45 90 5622-1x1 10P8C S-Y	
		DRAWING NO. E5681001	SIZE A3
		PART NO.	REV 0
		DO NOT SCALE DRAWING	SHEET X OF Y