




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2021-06-16			

9P	40.64	45.72
8P	35.56	40.64
7P	30.48	35.56
6P	25.4	30.48
5P	20.32	25.4
4P	15.24	20.32
3P	10.16	15.24
2P	5.08	10.16
NUMBER OF PINS	DIM. A	DIM. B

适应基板厚度: 1.2mm~1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC

额定电流: 7A

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ

耐压: 1500V AC/minute

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

2	PIN	n PCS	材质:黄铜,电镀:镀亮锡60u"MIN
1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:透明色
NO.	NAME	Q' TY	DESCRIPTION



深圳市韩下电子有限公司

DRAW :	黄彬	2021-06-16	TITLE:	插件针座	DRAW NAME:
DESIGN:			SERIES:	1501 SERIES	HX-CH5.08-6PWZ
CHECK:	张伟	2021-06-16	P/N:		DRAW NO.
APPROVED	罗小春	2021-06-16	REV. 1.00	SCALE N/A	UNIT: mm
CUSTOMER DRAWING					SHEET: 1/1
					+

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X° .	±3.00°
X. X	±0.35	X. X°	±2.00°
X. XX	±0.25	X. XX°	±1.00°
X. XXX	±0.15	X. XXX°	