

RoHS



REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		严亮	杜江	李永锋	2021-1-15

规格说明: Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:


1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 1.02kgf (MIN)
2. 端子保持力: Terminal Retention
1.2kgf (MIN)

原材料:Material:

1. 塑胶:Housing:
Hing Temperature Thernmaplastics,
UL 94V-0 LCP/PBT White/Black/Beige
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell: Copper Alloy C2680/SPCC


电镀:Finish:

1. 端子:Contact: Plated Gold in Mating Area;
Tin On Solder Talls
2. 外壳:Shell:
Nickel Plating


TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉焕精密有限公司			
UNIT	(MM)	ORIGINAL DATA 2021-1-15		TITLE USB BF 90度弯脚 PBT白胶	
X.	±0.55	DWG. 严亮		PART NO. USB-BF-001	
X.X	±0.35				
X.XX	±0.25				
X.XXX	±0.15				
ANGEL	±2°	CKD. 杜江		SCALE 1:1	SIZE A4
3RD. ANGLE'S 		APPD. 李永锋		SHEET 1/2	REV. A

RoHS

REV.	DESCRIPTION.	ECN NO.	DWG.	CKD.	APPD.	DATE.
A	NEW		严亮	杜江	李永锋	2021-1-15



- ① 1. PE真空盒(1Set).
2. 产品按照同一个方向摆放
- ② 100Pcs/盒, 5盒1扎用PE模包扎
- ③ 20盒/箱 (500pcs/扎*4扎=2000pcs) .



- ④ 依客户要求粘贴产品或ROHS标签.
- ⑤ 外箱用透明胶纸带封箱.
- ⑥ 每箱放置20盒*1, 若尾数箱在空间处加装填充物.

备注:

1. PE真空盒(1Set)

2. 每盒装成品100Pcs, 5盒1扎用PE模包扎;

3. 每箱装4扎, 每扎5盒, 共20盒(100*4*5=2000Pcs);

4. 外箱用透明胶纸带封箱;

5. 依客户要求粘贴产品标签或ROHS标签.

6; 纸箱规格 42*27*18CM

TOLERANCES UNLESS OTHERWISE SPECIFIED		东莞市辉焕精密有限公司			
UNIT (MM)	X.	±0.55	ORIGINAL DATA 2021-1-15	TITLE USB BF 90度弯脚PBT白胶	
	X.X	±0.35			
	X.XX	±0.25	DWG. 严亮		
	X.XXX	±0.15	CKD. 杜江	PART NO. USB-BF-001	SCALE 1:1
3RD.ANGLE'S			APPD. 李永锋	DWG NO. USB-BF-001	SIZE A4
				SHEET 1/2	REV. A