










[illegible][illegible][illegible][illegible]

								8	9																																																						
G	RoHS							序号	品名	材质																																																					
								①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																																					
								②	XH2.5直针WTB端子	铜合金/表面镀锡																																																					
F																																																															
E																																																															
D	带扣打K脚 2PIN TYPE 1(无K脚) TYPE 2(打K脚) SECTION A-A 常规2 Pin样式 技术指标(Technical Index): - 温度范围(Temperature range): -25° C~+85° C. - 额定电压(Rated voltage): 250V, AC. - 额定电流(Rated current): 3.0A AC, DC. - 接触电阻(Contact resistance): ≤20mΩ . - 耐压值(Withstanding voltage): 1000V AC/minute. - 绝缘电阻(Insulation resistance): ≥1000MΩ. - 产品料号(Product material No.): 适用线路板(PCB LAYOUT) <table border="1"> <thead> <tr> <th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr> </thead> <tbody> <tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr> <tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr> <tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr> <tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr> <tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr> <tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr> <tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr> <tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr> </tbody> </table>							CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0					
CKT	A	B	CKT	A	B																																																										
2	2.5	7.5	10	22.5	27.5																																																										
3	5.0	10.0	11	25.0	30.0																																																										
4	7.5	12.5	12	27.5	32.5																																																										
5	10.0	15.0	13	30.0	35.0																																																										
6	12.5	17.5	14	32.5	37.5																																																										
7	15.0	20.0	15	35.0	40.0																																																										
8	17.5	22.5	16	37.5	42.5																																																										
9	20.0	25.0																																																													
C																																																															
B																																																															
A					OPERATION			SCALE	FIT	深圳市连盛精密连接器有限公司																																																					
					X.X ±0.30	DRAW		UNIT	mm																																																						
					X.XX ±0.20	CHECK		SIZE	A4																																																						
					X.XXX ±0.10			SHEET	1/1	PART NO.	1130400117																																																				
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle ±3'	APPROVE		PROJ.	◆	TITLE:	XH-NA																																																				
	1	2	3	4	5	6	7	8	9																																																						

[illegible][illegible][illegible]

- [illegible]

[illegible][illegible][illegible]

RoHS								序号	品名	材质																																																												
								①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色白色																																																												
								②	XH2.5直针WTB端子	铜合金/表面镀锡																																																												
<table border="1"><thead><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr></thead><tbody><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></tbody></table>										CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0										
CKT	A	B	CKT	A	B																																																																	
2	2.5	7.5	10	22.5	27.5																																																																	
3	5.0	10.0	11	25.0	30.0																																																																	
4	7.5	12.5	12	27.5	32.5																																																																	
5	10.0	15.0	13	30.0	35.0																																																																	
6	12.5	17.5	14	32.5	37.5																																																																	
7	15.0	20.0	15	35.0	40.0																																																																	
8	17.5	22.5	16	37.5	42.5																																																																	
9	20.0	25.0																																																																				
技术指标(Technical Index)： 1. 温度范围(Temperature range)：-25° C~+85° C. 2. 额定电压(Rated voltage)：250V，AC. 3. 额定电流(Rated current)：3.0A AC,DC. 4. 接触电阻(Contact resistance)：≤20mΩ . 5. 耐压值(Withstanding voltage)：1000V AC/minute. 6. 绝缘电阻(Insulation resistance)：≥1000MΩ. 7. 产品料号(Product material No.)：																																																																						
<table border="1"><thead><tr><th colspan="4"></th><th colspan="2">OPERATION</th><th rowspan="2">DRAW</th><th rowspan="2">SCALE</th><th rowspan="2">FIT</th><th colspan="2" rowspan="2">深圳市连盛精密连接器有限公司</th></tr><tr><th colspan="4"></th><th>X.X</th><th>±0.30</th></tr></thead><tbody><tr><td colspan="4"></td><td>X.XX</td><td>±0.20</td><td>CHECK</td><td></td><td>UNIT</td><td>mm</td><td rowspan="2">PART NO.</td><td rowspan="2">1130400117</td></tr><tr><td colspan="4"></td><td>X.XXX</td><td>±0.10</td><td></td><td></td><td>SIZE</td><td>A4</td></tr><tr><td colspan="4"></td><td>Angle</td><td>±3'</td><td>APPROVE</td><td></td><td>SHEET</td><td>1/1</td><td>TITLE:</td><td rowspan="2">XH-NA</td></tr><tr><td>REV</td><td>DATE</td><td>MODIFICATION DESCRIPTION</td><td>CHANGE</td><td>DIM</td><td>TOL</td><td></td><td>PROJ.</td><td></td><td></td></tr></tbody></table>														OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司						X.X	±0.30					X.XX	±0.20	CHECK		UNIT	mm	PART NO.	1130400117					X.XXX	±0.10			SIZE	A4					Angle	±3'	APPROVE		SHEET	1/1	TITLE:	XH-NA	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL		PROJ.		
				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																													
				X.X	±0.30																																																																	
				X.XX	±0.20	CHECK		UNIT	mm	PART NO.	1130400117																																																											
				X.XXX	±0.10			SIZE	A4																																																													
				Angle	±3'	APPROVE		SHEET	1/1	TITLE:	XH-NA																																																											
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL		PROJ.																																																															
1	2	3	4	5	6	7	8	9																																																														

[illegible][illegible][illegible][illegible][illegible]

G	RoHS							序号	品名	材质																																																																																													
F								①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色白色																																																																																													
E								②	XH2.5直针WTB端子	铜合金/表面镀锡																																																																																													
D								带扣打K脚 2PIN																																																																																															
C								常规2 Pin样式																																																																																															
B	技术指标(Technical Index): 1. 温度范围(Temperature range): -25° C~+85° C. 2. 额定电压(Rated voltage): 250V, AC. 3. 额定电流(Rated current): 3.0A AC, DC. 4. 接触电阻(Contact resistance): ≤20mΩ . 5. 耐压值(Withstanding voltage): 1000V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ. 7. 产品料号(Product material No.):							 适用线路板(PCB LAYOUT)																																																																																															
A	<table border="1"><thead><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr></thead><tbody><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></tbody></table>							CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0				<table border="1"><thead><tr><th colspan="2">OPERATION</th><th rowspan="2">DRAW</th><th rowspan="2">SCALE</th><th rowspan="2">FIT</th><th rowspan="5">深圳市连盛精密连接器有限公司</th></tr><tr><th></th><th></th></tr><tr><td>X.X</td><td>±0.30</td><td rowspan="3">CHECK</td><td>UNIT</td><td>mm</td><th rowspan="2">PART NO.</th><th rowspan="2">1130400117</th></tr><tr><td>X.XX</td><td>±0.20</td><td>SIZE</td><td>A4</td></tr><tr><td>X.XXX</td><td>±0.10</td><td>SHEET</td><td>1/1</td><th>TITLE:</th><th>XH-NA</th></tr><tr><td>Angle</td><td>±3'</td><td>APPROVE</td><td>PROJ.</td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td></tr></thead></table>			OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司			X.X	±0.30	CHECK	UNIT	mm	PART NO.	1130400117	X.XX	±0.20	SIZE	A4	X.XXX	±0.10	SHEET	1/1	TITLE:	XH-NA	Angle	±3'	APPROVE	PROJ.				DIM	TOL					
CKT	A	B	CKT	A	B																																																																																																		
2	2.5	7.5	10	22.5	27.5																																																																																																		
3	5.0	10.0	11	25.0	30.0																																																																																																		
4	7.5	12.5	12	27.5	32.5																																																																																																		
5	10.0	15.0	13	30.0	35.0																																																																																																		
6	12.5	17.5	14	32.5	37.5																																																																																																		
7	15.0	20.0	15	35.0	40.0																																																																																																		
8	17.5	22.5	16	37.5	42.5																																																																																																		
9	20.0	25.0																																																																																																					
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																																		
X.X	±0.30	CHECK	UNIT	mm		PART NO.	1130400117																																																																																																
X.XX	±0.20		SIZE	A4																																																																																																			
X.XXX	±0.10		SHEET	1/1		TITLE:	XH-NA																																																																																																
Angle	±3'	APPROVE	PROJ.																																																																																																				
DIM	TOL																																																																																																						
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE																																																																																																			
	1	2	3	4	5	6	7	8	9																																																																																														

[illegible][illegible][illegible][illegible][illegible]

	2	3	4	5	6	7	8	9																																																													
G	RoHS							序号	品名	材质																																																											
								①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																																											
F								②	XH2.5直针WTB端子	铜合金/表面镀锡																																																											
E																																																																					
D																																																																					
C	技术指标(Technical Index): - 温度范围(Temperature range): -25° C~+85° C. - 额定电压(Rated voltage): 250V, AC. - 额定电流(Rated current): 3.0A AC, DC. - 接触电阻(Contact resistance): ≤20mΩ . - 耐压值(Withstanding voltage): 1000V AC/minute. - 绝缘电阻(Insulation resistance): ≥1000MΩ. - 产品料号(Product material No.):																																																																				
B																																																																					
A	<table border="1"><thead><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr></thead><tbody><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></tbody></table>							CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0											
CKT	A	B	CKT	A	B																																																																
2	2.5	7.5	10	22.5	27.5																																																																
3	5.0	10.0	11	25.0	30.0																																																																
4	7.5	12.5	12	27.5	32.5																																																																
5	10.0	15.0	13	30.0	35.0																																																																
6	12.5	17.5	14	32.5	37.5																																																																
7	15.0	20.0	15	35.0	40.0																																																																
8	17.5	22.5	16	37.5	42.5																																																																
9	20.0	25.0																																																																			
	<table border="1"><thead><tr><th>REV</th><th>DATE</th><th>MODIFICATION DESCRIPTION</th><th>CHANGE</th><th>OPERATION</th><th>DRAW</th><th>SCALE</th><th>FIT</th><th colspan="2">深圳市连盛精密连接器有限公司</th></tr></thead><tbody><tr><td></td><td></td><td></td><td></td><td>X.X</td><td>±0.30</td><td></td><td></td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>X.XX</td><td>±0.20</td><td></td><td></td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>X.XXX</td><td>±0.10</td><td></td><td></td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>Angle</td><td>±3'</td><td></td><td></td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>DIM</td><td>TOL</td><td></td><td></td><td colspan="2"></td></tr></tbody></table>							REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司						X.X	±0.30									X.XX	±0.20									X.XXX	±0.10									Angle	±3'									DIM	TOL						
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																													
				X.X	±0.30																																																																
				X.XX	±0.20																																																																
				X.XXX	±0.10																																																																
				Angle	±3'																																																																
				DIM	TOL																																																																
	1	2	3	4	5	6	7	8	9																																																												