




[illegible][illegible]

	-	2	3	4	5	6	7	8	9																																																				
G	RoHS								<table border="1"><tr><td>序号</td><td>品名</td><td>材质</td></tr><tr><td>①</td><td>XH2.5直针WTB胶芯</td><td>PA66 UL94V-0 米色 白色</td></tr><tr><td>②</td><td>XH2.5弯针WTB端子</td><td>铜合金/表面镀锡</td></tr></table>	序号	品名	材质	①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色	②	XH2.5弯针WTB端子	铜合金/表面镀锡	G																																										
序号	品名	材质																																																											
①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																																											
②	XH2.5弯针WTB端子	铜合金/表面镀锡																																																											
F		2 Pin样式							F																																																				
E									E																																																				
D			TYPE 1(无K脚)	TYPE 2(打K脚)					D																																																				
C	技术指标(Technical Index): 1.温度范围(Temperature range):-25°C~+85°C. 2.额定电压(Rated voltage):250V.AC. 3.额定电流(Rated current):3.OAAC,DC. 4.接触电阻(Contact resistance):≤20mΩ . 5.耐压值(Withstanding voltage):1000V AC/minute. 6.绝缘电阻(Insulation resistance):≥1000MΩ. 7.产品料号(Product material No.):					<table border="1"><thead><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr></thead><tbody><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></tbody></table>	CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0				C
CKT	A	B	CKT	A	B																																																								
2	2.5	7.5	10	22.5	27.5																																																								
3	5.0	10.0	11	25.0	30.0																																																								
4	7.5	12.5	12	27.5	32.5																																																								
5	10.0	15.0	13	30.0	35.0																																																								
6	12.5	17.5	14	32.5	37.5																																																								
7	15.0	20.0	15	35.0	40.0																																																								
8	17.5	22.5	16	37.5	42.5																																																								
9	20.0	25.0																																																											
B									B																																																				
A				<table border="1"><tr><td colspan="2">OPERATION</td><td rowspan="4">DRAW</td><td rowspan="4">SCALE</td><td rowspan="4">FIT</td><td colspan="2" rowspan="4">深圳市连盛精密连接器有限公司</td></tr><tr><td>X.X</td><td>±0.30</td></tr><tr><td>X.XX</td><td>±0.20</td></tr><tr><td>X.XXX</td><td>±0.10</td></tr><tr><td>Angle</td><td>±3'</td><td rowspan="2">CHECK</td><td rowspan="2">SIZE</td><td rowspan="2">A4</td><td rowspan="2">PART NO.</td><td rowspan="2">1130400154</td></tr><tr><td>DIM</td><td>TOL</td><td rowspan="2">APPROVE</td><td rowspan="2">SHEET</td><td rowspan="2">1/1</td><td rowspan="2">TITLE:</td><td rowspan="2">XH-NAW</td></tr><tr><td>REV</td><td>DATE</td><td>MODIFICATION DESCRIPTION</td><td>CHANGE</td><td>PROJECT</td><td>◆</td></tr></table>	OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	X.XXX	±0.10	Angle	±3'	CHECK	SIZE	A4	PART NO.	1130400154	DIM	TOL	APPROVE	SHEET	1/1	TITLE:	XH-NAW	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	PROJECT	◆										A														
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																								
X.X	±0.30																																																												
X.XX	±0.20																																																												
X.XXX	±0.10																																																												
Angle	±3'	CHECK	SIZE	A4	PART NO.	1130400154																																																							
DIM	TOL						APPROVE	SHEET	1/1	TITLE:	XH-NAW																																																		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	PROJECT	◆																																																								
	1	2	3	4	5	6	7	8	9																																																				



-

2

3

4

5

6

7

8

9

G

F

E

D

C

B

A

RoHS

序号	品名	材质
①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色
②	XH2.5弯针WTB端子	铜合金/表面镀锡





技术指标(Technical Index):

- 1.温度范围(Temperature range):-25° C~+85° C.
- 2.额定电压(Rated voltage):250V, AC.
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance):≤20mΩ .
- 5.耐压值(Withstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.
- 7.产品料号(Product material No.):


适用线路板(PCB LAYOUT)

CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0			

				OPERATION		DRAW				SCALE	FIT	深圳市连盛精密连接器有限公司 PART NO. 1130400154 TITLE: XH-NAW		
				X.X ±0.30						UNIT	mm			
				X.XX ±0.20		CHECK				SIZE	A4			
				X.XXX ±0.10						SHEET	1/1			
				Angle ±3°		APPROVE				PROJ.	◆			
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL								
1		2		3	4		5		6		7		8	9

[illegible][illegible][illegible][illegible]

- [illegible]

[illegible]