










PCB.焊接图



电 路 图

H	L
3.3	2.80
3.8	
4.3	3.15
4.5	
5.0	
5.5	
7.0	

主要技术规格:

- 1.额定值: 50mA DC12V
- 2.接触电阻: $\leq 50m\Omega$
- 3.操作力: $250\pm 30gf$
- 4.行程: $0.30\pm 0.1mm$
- 5.绝缘电阻: $\geq 100M\Omega$
- 6.抗电强度: 250V 50HZ 1Min.
- 7.寿命: 100,000 Cycles
- 8.防水等级: IP67
- 9.防银迁移: 60V, 85℃, 90%RH/60H

T S - 1 0 2 0 - A R L - - - - - B

弹片: A: 不锈钢 B: 覆磷铜
定位柱: R: 无柱
安装方式: W: 贴片 L: 插件 U: 包脚 F: 沉板
高度: 033: 3.3H 038: 3.8H 070: 7.0H
力度: 16: 160g 26: 260g
按键颜色: B: 黑 R: 红

序号	零件名称	材料规格	备注
1	按钮	PPA	耐温280℃ (黑色)
2	盖板	不锈钢	/
3	防水垫	硅胶	耐温280℃ (黑色)
4	簧片	不锈钢	覆银
5	基座	PPA	耐温280℃ (黑色)
6	引脚、触点	黄铜	镀银

MANUFACTURE DWG

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

>0.5~2: ± 0.10 >2~5: ± 0.25 >5~10: ± 0.30

ANGLES:

 $\pm 0.5^\circ$ 东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., Ltd

TITLE:

TACT SWITCH

PAR

DWN

CHKD

APVD

SCALE 1:1

SIZE: A4

TS-1020-ARLXXX-B

UNIT: MM

SHEET: 1F1

REV: A

CUSTOMER COPY

