

		2	3	4	5	6	7	8	9																																																										
G		RoHS						序号	品名	材质	G																																																								
								①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																																									
								②	XH2.5直针WTB端子	铜合金/表面镀锡																																																									
F																																																																			
E																																																																			
D				TYPE 1 (无K脚)		TYPE 2 (打K脚)		SECTION A-A																																																											
C		技术指标 (Technical Index): - 温度范围 (Temperature range): -25° C~+85° C. - 额定电压 (Rated voltage): 250V, AC. - 额定电流 (Rated current): 3.0A AC, DC. - 接触电阻 (Contact resistance): ≤20mΩ . - 耐压值 (Withstanding voltage): 1000V AC/minute. - 绝缘电阻 (Insulation resistance): ≥1000MΩ. - 产品料号 (Product material No.):						<table><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></table>						CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0			
CKT	A	B	CKT	A	B																																																														
2	2.5	7.5	10	22.5	27.5																																																														
3	5.0	10.0	11	25.0	30.0																																																														
4	7.5	12.5	12	27.5	32.5																																																														
5	10.0	15.0	13	30.0	35.0																																																														
6	12.5	17.5	14	32.5	37.5																																																														
7	15.0	20.0	15	35.0	40.0																																																														
8	17.5	22.5	16	37.5	42.5																																																														
9	20.0	25.0																																																																	
B																																																																			
A					OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司																																																							
					X.X	±0.30				UNIT	mm																																																								
					X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1130400118																																																						
					X.XXX	±0.10				SHEET	1/1																																																								
		REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE		PROJ.		TITLE:	XH-NA																																																						
		1	2	3	4	5	6	7	8	9																																																									