







RoHS




| 序号 | 品名           | 材质                    |
|----|--------------|-----------------------|
| ①  | XH2.5直针WTB胶芯 | PA66 UL94V-0 米色<br>白色 |
| ②  | XH2.5弯针WTB端子 | 铜合金/表面镀锡              |




2 Pin样式



SECTION A-A



TYPE 1 (无K脚)




TYPE 2 (打K脚)

| CKT | A    | B    | CKT | A    | B    |
|-----|------|------|-----|------|------|
| 2   | 2.5  | 7.5  | 10  | 22.5 | 27.5 |
| 3   | 5.0  | 10.0 | 11  | 25.0 | 30.0 |
| 4   | 7.5  | 12.5 | 12  | 27.5 | 32.5 |
| 5   | 10.0 | 15.0 | 13  | 30.0 | 35.0 |
| 6   | 12.5 | 17.5 | 14  | 32.5 | 37.5 |
| 7   | 15.0 | 20.0 | 15  | 35.0 | 40.0 |
| 8   | 17.5 | 22.5 | 16  | 37.5 | 42.5 |
| 9   | 20.0 | 25.0 |     |      |      |

技术指标 (Technical Index):

1. 温度范围 (Temperature range):  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
2. 额定电压 (Rated voltage): 250V, AC.
3. 额定电流 (Rated current): 3.0A, AC, DC.
4. 接触电阻 (Contact resistance):  $\leq 20\text{m}\Omega$ .
5. 耐压值 (Withstanding voltage): 1000V AC/minute.
6. 绝缘电阻 (Insulation resistance):  $\geq 1000\text{M}\Omega$ .
7. 产品料号 (Product material No.):



深圳市连盛精密连接器有限公司

PART NO.

1130400150

TITLE:

XH-NAW

OPERATION

DRAW

SCALE

FIT

X.X

±0.30

UNIT

mm

X.XX

±0.20

CHECK

SIZE

A4

X.XXX

±0.10

APPROVE

SHEET

1/1

Angle

±3°

PROJ.

◆

DIM

TOL

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9