






电 路 图

H	L
3.3	2.8
3.8	
4.3	3.15
4.5	
5.0	
5.5	
7.0	



PCB.焊接图

T S - 1 0 2 2 - A R L

主要技术规格:

- 1.额定值: 50mA DC12V
- 2.接触电阻: $\leq 50\text{m}\Omega$
- 3.操作力: $250\pm 30\text{gf}$
- 4.行程: $0.30\pm 0.1\text{mm}$
- 5.绝缘电阻: $\geq 100\text{M}\Omega$
- 6.抗电强度: 250V 50HZ 1Min.
- 7.寿命: 100,000 Cycles
- 8.防水等级: IP67
- 9.防银迁移: 60V, 85℃, 90%RH/60H

弹片: A:不锈钢 B:覆磷铜
定位柱: R:无柱
安装方式: W:贴片 L:插件 U:包脚 F:沉板
高度: 033:3.3H 038:3.8H 055:5.5H 070:7.0H
力度: 16:160g 26:260g
按键颜色: B:黑 R:红

序号	零件名称	材料规格	备注
1	按钮	PPA	耐温280℃ (黑色/红色)
2	盖板	不锈钢	/
3	簧片	不锈钢	覆银
4	基座	PPA	耐温280℃ (黑色)
5	引脚、触点	黄铜	镀银
6	防水垫	硅胶	耐温280℃ (黑色)

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

ANGLES:

>0.5~2:±0.10

±0.5°

>2~5:±0.25

>5~10:±0.30

TITLE:
TACT SWITCH

PAR TS-1022-ARLXXX-X

DWN

CHKD

APVD

SCALE 1:1 UNIT:MM

SIZE:A4 SHEET:1F1 REV:A

CUSTOMER COPY