






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




PIN	P/N
ø1.0	DC002-10C
ø1.3	DC002-13C




PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 12V 2A
Contact resistance	≤30mΩ
Insulation resistance	>100MΩ DC500V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20C°~+70C°
service life	5000cycles



SCHEMATIC

6	弹片	1	H62	镀银
5	插片	1	H62	镀银
4	平片	1	H62	镀银
3	中心针	1	H62	铜锡
2	盖板	1	PPA	黑
1	底座	1	PPA	黑
序号	名称	数量	材料	备注
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X'.:±5°	PART NO. DC002-NC	TITLE: DC SOCKET	
X.X:±0.25	X.X':±1°			
X.XX:±0.15				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1