







RoHS




序号	品名	材质
①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色
②	XH2.5弯针WTB端子	铜合金/表面镀锡




2 Pin样式



SECTION A-A




TYPE 1 (无K脚)



TYPE 2 (打K脚)

技术指标 (Technical Index):

- 温度范围 (Temperature range): -25° C ~ +85° C.
- 额定电压 (Rated voltage): 250V, AC.
- 额定电流 (Rated current): 3.0A, AC, DC.
- 接触电阻 (Contact resistance): ≤20mΩ.
- 耐压值 (Withstanding voltage): 1000V AC/minute.
- 绝缘电阻 (Insulation resistance): ≥1000MΩ.
- 产品料号 (Product material No.):



适用线路板 (PCB LAYOUT)

深圳市连盛精密连接器有限公司

PART NO.

1130400088

TITLE:

XH-NAW

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9