






[illegible]

RoHS		2	3	4	5	6	7	8	9																																																								
									序号	品名	材质																																																						
									①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色白色																																																						
									②	XH2.5弯针WTB端子	铜合金/表面镀锡																																																						
		技术指标(Technical Index): 1. 温度范围(Temperature range): -25° C~+85° C. 2. 额定电压(Rated voltage): 250V, AC. 3. 额定电流(Rated current): 3.0A AC, DC. 4. 接触电阻(Contact resistance): ≤20mΩ . 5. 耐压值(Withstanding voltage): 1000V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ. 7. 产品料号(Product material No.):																																																															
									<table><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></table>			CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0			
CKT	A	B	CKT	A	B																																																												
2	2.5	7.5	10	22.5	27.5																																																												
3	5.0	10.0	11	25.0	30.0																																																												
4	7.5	12.5	12	27.5	32.5																																																												
5	10.0	15.0	13	30.0	35.0																																																												
6	12.5	17.5	14	32.5	37.5																																																												
7	15.0	20.0	15	35.0	40.0																																																												
8	17.5	22.5	16	37.5	42.5																																																												
9	20.0	25.0																																																															
									<table><tr><th colspan="2">OPERATION</th><th rowspan="2">DRAW</th><th rowspan="2">SCALE</th><th rowspan="2">FIT</th><th colspan="2" rowspan="2">深圳市连盛精密连接器有限公司</th></tr><tr><th>X.X</th><th>±0.30</th></tr><tr><th colspan="2">X.XX</th><th>±0.20</th><th rowspan="2">CHECK</th><th rowspan="2">SIZE</th><th rowspan="2">A4</th><th rowspan="2">PART NO.</th><th rowspan="2">1130400081</th></tr><tr><th colspan="2">X.XXX</th><th>±0.10</th></tr><tr><th colspan="2">Angle</th><th>±3°</th><th rowspan="2">APPROVE</th><th rowspan="2">SHEET</th><th rowspan="2">1/1</th><th rowspan="2">TITLE:</th><th rowspan="2">XH-AW</th></tr><tr><th>REV</th><th>DATE</th><th>MODIFICATION DESCRIPTION</th><th>CHANGE</th><th>DIM</th><th>TOL</th></tr></table>			OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX		±0.20	CHECK	SIZE	A4	PART NO.	1130400081	X.XXX		±0.10	Angle		±3°	APPROVE	SHEET	1/1	TITLE:	XH-AW	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL																				
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																												
X.X	±0.30																																																																
X.XX		±0.20	CHECK	SIZE	A4	PART NO.	1130400081																																																										
X.XXX		±0.10																																																															
Angle		±3°	APPROVE	SHEET	1/1	TITLE:	XH-AW																																																										
REV	DATE	MODIFICATION DESCRIPTION						CHANGE	DIM	TOL																																																							
1	2	3	4	5	6	7	8	9																																																									

[illegible][illegible]

-

2

3

4

5

6

7

8

9

G

F

E

D

C

B

A

RoHS

序号	品名	材质
①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色
②	XH2.5弯针WTB端子	铜合金/表面镀锡

②

2.5±0.10(PITCH)

DIMA±0.20

DIMB±0.25

2 Pin样式

(4.5)

(5.2)

SECTION A-A

A

0.64±0.05

5.75±0.25

7.00±0.25

3.40±0.20

7.2±0.25

TYPE 1(无K脚)

0.80±0.20

TYPE 2(打K脚)

DIMA±0.10

2.50±0.10

Ø0.90^{+0.08}/_{-0.05}

适用线路板(PCB LAYOUT)

技术指标(Technical Index)：

1.温度范围(Temperature range)：-25° C~+85° C.

2.额定电压(Rated voltage)：250V，AC.

3.额定电流(Rated current)：3.0A AC,DC.

4.接触电阻(Contact resistance)：≤20mΩ .

5.耐压值(Withstanding voltage)：1000V AC/minute.

6.绝缘电阻(Insulation resistance)：≥1000MΩ.

7.产品料号(Product material No.)：

CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0			

OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
X.X ±0.30	CHECK	UNIT	mm	PART NO.	1130400081
X.XX ±0.20		SIZE	A4		
X.XXX ±0.10		SHEET	1/1		
Angle ±3°	APPROVE	PROJECT	TITLE:	XH-NAW	
DIM TOL					

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4


5

6


7

8

9

[illegible][illegible][illegible]

- [illegible]

[illegible]