








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN





PIN	P/N
ø2.0	DC012A-20C
ø2.5	DC012A-25C



PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 24V 2.5A
Contact resistance	≤30mΩ
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-20C°~+70C°
service life	5000cycles



6	弹片	1	H65	镀银		
5	插片	1	H62	镀银		
4	平片	1	H62	镀银		
3	中心针	1	H62	铜锡		
2	盖板	1	PPA	黑		
1	底座	1	PPA	黑		
序号	名称	数量	材料	备注		
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.:±0.30	X'.:±5°	PART NO. DC012A-NC		TITLE: DC SOCKET		
X.X:±0.25	X.X':±1°					
X.XX:±0.15		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm					
MATERILA	— — —	CHED: Olvia			SCALE	SHEET
FINISH	— — —	APPD: Ava			N:A	1/1