










PCB.焊接图



H	L
4.3	3.5
4.5	
5.0	
5.5	
7.0	



电 路 图

主要技术规格:

- 1.额定值: 50mA DC12V
- 2.接触电阻: $\leq 50\text{m}\Omega$
- 3.操作力: $250\pm 30\text{gf}$
- 4.行程: $0.30\pm 0.1\text{mm}$
- 5.绝缘电阻: $\geq 100\text{M}\Omega$
- 6.抗电强度: 250V 50HZ 1Min.
- 7.寿命: 100,000 Cycles
- 8.防水等级: IP67
- 9.防银迁移: 60V, 85℃, 90%RH/60H

弹片:

A:不锈钢

B:覆磷铜

定位柱:

R:无柱

安装方式:

W:贴片

L:插件

U:包脚

F:沉板

高度:

043:4.3H

045:4.5H

050:5.0H

055:5.5H

070:7.0H

力度:

16:160g

26:260g

按键颜色:

B:黑

R:红

TS-1021-ARW

序号	零件名称	材料规格	备注
1	按钮	PPA	耐温280℃ (黑色/红色)
2	盖板	不锈钢	/
3	防水垫	硅胶	耐温280℃ (黑色)
4	簧片	不锈钢	覆银
5	基座	PPA	耐温280℃ (黑色)
6	引脚、触点	黄铜	镀银

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

>0.5~2:±0.10

>2~5:±0.25

>5~10:±0.30

ANGLES:

±0.5°



TITLE:

TACT SWITCH

PAR

DWN

CHKD

APVD

SCALE1:1

SIZE:A4

UNIT:MM

SHEET:1F1

REV:A

