









REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




PIN	P/N
Ø2.0	DC-060B-20C
Ø2.5	DC-060B-25C




PCB.WELDING DRAWING (TOLERANCE:±0.05)


Main technical performance	
Rated electrical load	DC 24V 8A
Contact resistance	≤0.03Ω
Insulation resistance	≥100MΩ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-40℃~+85℃
service life	5000cycles



RECOMMEND PULG



SCHEMATIC

5	圓針	1	黃銅棒	鍍銀	
4	蓋片	1	H62黃銅帶(Y)	鍍銀	
3	簧片	1	磷銅帶	銅錫	
2	屏蔽罩	1	H62黃銅帶(Y)	黑	
1	基座	1	PPA	黑	
序号	名称	数量	材料	备注	
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO.		TITLE:	
X.X:±0.25	X.X':±1°	DC-060B-NC		DC SOCKET	
X.XX:±0.15		DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —			SCALE	SHEET
				N:A	1/1