










RoHS

| 序号 | 品名           | 材质                             |
|----|--------------|--------------------------------|
| ①  | PH2.0直针WTB胶芯 | 米色<br>PA66 UL94V-0<br>白色<br>红色 |
| ②  | PH2.0弯针WTB端子 | 铜合金/表面镀锡                       |




SECTION A-A



TYPE 1(无K脚)

TYPE 2(打K脚)



技术指标(Technical Index):

1. 工作温度(Temperature range): -40° C~85° C.
2. 额定电压(Rated voltage): 250V DC/AC(rms).
3. 额定电流(Rated current): 2.0A.
4. 接触电阻(Contact resistance): ≤25mΩ.
5. 耐压值(Withstanding voltage): 500V AC/minute.
6. 绝缘电阻(Insulation resistance): ≥1000MΩ.
7. 产品料号(Product material No.):

| CKT | A    | B    | CKT | A    | B    |
|-----|------|------|-----|------|------|
| 2   | 2.0  | 6.0  | 12  | 22.0 | 26.0 |
| 3   | 4.0  | 8.0  | 13  | 24.0 | 28.0 |
| 4   | 6.0  | 10.0 | 14  | 26.0 | 30.0 |
| 5   | 8.0  | 12.0 | 15  | 28.0 | 32.0 |
| 6   | 10.0 | 14.0 | 16  | 30.0 | 34.0 |
| 7   | 12.0 | 16.0 | 17  | 32.0 | 36.0 |
| 8   | 14.0 | 18.0 | 18  | 34.0 | 38.0 |
| 9   | 16.0 | 20.0 | 19  | 36.0 | 40.0 |
| 10  | 18.0 | 22.0 | 20  | 38.0 | 42.0 |
| 11  | 20.0 | 24.0 |     |      |      |

深圳市连盛精密连接器有限公司

|     |      |                          |        | OPERATION |       | DRAW    |  |  | SCALE | FIT   |
|-----|------|--------------------------|--------|-----------|-------|---------|--|--|-------|-------|
|     |      |                          |        | X.X       | ±0.30 |         |  |  |       | UNIT  |
|     |      |                          |        | X.XX      | ±0.20 | CHECK   |  |  | SIZE  | A4    |
|     |      |                          |        | X.XXX     | ±0.10 |         |  |  |       | SHEET |
|     |      |                          |        | Angle     | ±3°   | APPROVE |  |  |       |       |
| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | DIM       | TOL   |         |  |  |       | PROJ. |