

RoHS		2	3	4	5	6	7	8	9
		序号		品名		材质			
		①		VH3.96直针WTB胶芯		PA66 UL94V-0 米色 白色			
		②		VH3.96直针WTB端子		铜合金/表面镀锡			
						技术指标(Technical Index): 1. 温度范围(Temperature range): -25° C~-85° C. 2. 额定电压(Rated voltage): 250V, AC, DC. 3. 额定电流(Rated current): 7.0A AC, DC. 4. 接触电阻(Contact resistance): ≤20mΩ . 5. 耐压值(Withstanding voltage): 1500V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ.			
		适用线路板 (PCB LAYOUT)							