






PCB.电路图
CIRCUIT DIAGRAM

H	L
4.3	2.95
4.5	3.45
5.0	3.95
.....	
9.5	8.45
10.0	8.95



T S - 1 0 1 9 - A R L - B

弹片:
A:不锈钢
B:覆磷铜

定位柱:
R:无柱

安装方式:
W:贴片
L:插件
U:包脚
F:沉板


高度:
043:4.3H
045:4.5H
.....
100:10.0H

力度:
16:160g
26:260g

按键颜色:
B:黑
R:红

主要技术规格:

- 额定值: 50mA DC12V
- 接触电阻: $\leq 50m\Omega$
- 操作力: $F \pm 40gf$
- 行程: $0.25 \pm 0.1mm$
- 绝缘电阻: $\geq 100M\Omega$
- 抗电强度: 250V 50HZ 1Min.
- 寿命: 100,000 Cycles
- 防水等级: IP67
- 防银迁移: 60V, 85℃, 90%RH/60H



PCB.焊接图

PCB.WELDING DRAWING

序号	零件名称	材料规格	备注
1	按钮	PPA	耐温280℃ (黑色)
2	盖板	PPA	耐温280℃ (黑色)
3	防水垫	硅胶	耐温280℃ (黑色)
4	簧片	不锈钢	覆银
5	基座	PPA	耐温280℃ (黑色)
6	引脚、触点	黄铜	镀银
7	支架	黄铜	镀锡

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:
TACT SWITCH

DECIMALS:

ANGLES:

>0.5~2:±0.10

±0.5°

>2~5:±0.25

>5~10:±0.30

PAR	TS-1019-ARLXXX-B
DWN	
CHKD	
APVD	
SCALE:1:1	UNIT:MM
SIZE:A4	SHEET:1F1
	REV:A

CUSTOMER COPY