








RoHS



SECTION A-A

技术指标 (Technical Index):

- 工作温度 (Temperature range): -25° C~85° C.
- 额定电压 (Rated voltage): 250V DC/AC(rms).
- 额定电流 (Rated current): 2.0A AC, DC.
- 接触电阻 (Contact resistance): ≤25mΩ.
- 耐压值 (Withstanding voltage): 500V AC/minute.
- 绝缘电阻 (Insulation resistance): ≥1000MΩ.
- 产品料号 (Product material No.):

TYPE 1 (无K脚)

TYPE 2 (打K脚)

| CKT | A    | B    | CKT | A    | B    |
|-----|------|------|-----|------|------|
| 2   | 2.0  | 6.0  | 12  | 22.0 | 26.0 |
| 3   | 4.0  | 8.0  | 13  | 24.0 | 28.0 |
| 4   | 6.0  | 10.0 | 14  | 26.0 | 30.0 |
| 5   | 8.0  | 12.0 | 15  | 28.0 | 32.0 |
| 6   | 10.0 | 14.0 | 16  | 30.0 | 34.0 |
| 7   | 12.0 | 16.0 | 17  | 32.0 | 36.0 |
| 8   | 14.0 | 18.0 | 18  | 34.0 | 38.0 |
| 9   | 16.0 | 20.0 | 19  | 36.0 | 40.0 |
| 10  | 18.0 | 22.0 | 20  | 38.0 | 42.0 |
| 11  | 20.0 | 24.0 |     |      |      |

| 序号 | 品名           | 材质                          |
|----|--------------|-----------------------------|
| ①  | PH2.0弯针WTB胶芯 | PA66 UL94V-0 米色<br>白色<br>红色 |
| ②  | PH2.0直针WTB端子 | 铜合金/表面镀锡                    |

深圳市连盛精密连接器有限公司

|     |      |                          |        |           |       |         |  |  |       |                                                                                       |                |            |
|-----|------|--------------------------|--------|-----------|-------|---------|--|--|-------|---------------------------------------------------------------------------------------|----------------|------------|
|     |      |                          |        | OPERATION |       | DRAW    |  |  | SCALE | FIT                                                                                   | 深圳市连盛精密连接器有限公司 |            |
|     |      |                          |        | X.X       | ±0.30 |         |  |  | UNIT  | mm                                                                                    |                |            |
|     |      |                          |        | X.XX      | ±0.20 | CHECK   |  |  | SIZE  | A4                                                                                    | PART NO.       | 1130300001 |
|     |      |                          |        | X.XXX     | ±0.10 |         |  |  | SHEET | 1/1                                                                                   |                |            |
|     |      |                          |        | Angle     | ±3°   | APPROVE |  |  |       |                                                                                       | TITLE:         | PH-NA      |
| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | DIM       | TOL   |         |  |  | PROJ. |  |                |            |