







RoHS

序号	品名	材质
①	HA2.5弯针WTB胶芯	PA66 UL94V-0 米色 白色
②	XH2.5直针WTB端子	铜合金/表面镀锡




技术指标 (Technical Index):

- 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
- 额定电压 (Rated voltage): 250V, AC.
- 额定电流 (Rated current): 3.0A AC, DC.
- 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
- 耐压值 (Withstanding voltage): 1000V AC/minute.
- 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.
- 产品料号 (Product material No.):

TYPE 1 (无K脚)

TYPE 2 (打K脚)



SECTION A-A

CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0			

				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					
				X.XX	±0.20	CHECK	UNIT	mm	PART NO. 1130400156	
				X.XXX	±0.10					
				Angle	±3°	APPROVE	SHEET	1/1	TITLE: XHB-NA	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL					

1 2 3 4 5 6 7 8 9