








RoHS



技术指标(Technical Index):

- 工作温度(Temperature range): -25° C~85° C.
- 额定电压(Rated voltage): 250V DC/AC(rms).
- 额定电流(Rated current): 2.0A AC, DC.
- 接触电阻(Contact resistance): ≤25mΩ.
- 耐压值(Withstanding voltage): 500V AC/minute.
- 绝缘电阻(Insulation resistance): ≥1000MΩ.
- 产品料号(Product material No.):

TYPE 1 (无K脚)

TYPE 2 (打K脚)

SECTION A-A

CKT	A	B	CKT	A	B
2	2.0	6.0	12	22.0	26.0
3	4.0	8.0	13	24.0	28.0
4	6.0	10.0	14	26.0	30.0
5	8.0	12.0	15	28.0	32.0
6	10.0	14.0	16	30.0	34.0
7	12.0	16.0	17	32.0	36.0
8	14.0	18.0	18	34.0	38.0
9	16.0	20.0	19	36.0	40.0
10	18.0	22.0	20	38.0	42.0
11	20.0	24.0			

序号	品名	材质
①	PH2.0弯针WTB胶芯	PA66 UL94V-0 米色 白色 红色
②	PH2.0直针WTB端子	铜合金/表面镀锡

				OPERATION		DRAW				SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT	mm		
				X.XX	±0.20	CHECK				SIZE	A4		
				X.XXX	±0.10					SHEET	1/1	PART NO.	1130300168
				Angle	±3°	APPROVE						TITLE:	PH-NA
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL					PROJ.		