

RoHS

序号	品名	材质
①	2.50 M型卧式WTB胶芯	LCP UL94V-0 本色
②	2.50 M型卧式WTB端子	铜合金/表面镀锡
③	2.50 M型卧式WTB焊片	铜合金/表面镀锡

技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
- 工作温度: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 适用线规: AWG#28~#22.
- 额定电压: 250V DC/AC(rms).
- 额定电流: 3.0A.
- 接触电阻: $\leq 20\text{m}\Omega$.
- 耐压值: 1000V AC/minute.
- 绝缘电阻: $\geq 1000\text{M}\Omega$.
- 产品料号:

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00

2P 结构

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ± 0.30

UNIT

mm

X.XX ± 0.20

CHECK

SIZE

A4

PART NO.

1130400137

X.XXX ± 0.10

Angle $\pm 3^{\circ}$

APPROVE

SHEET

1/1

TITLE:

XH-AWR

DIM TOL

PROJ.

◆

