












RoHS

序号	品名	材质
①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色
②	XH2.5弯针WTB端子	铜合金/表面镀锡



技术指标 (Technical Index):

- 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
- 额定电压 (Rated voltage): 250V, AC.
- 额定电流 (Rated current): 3.0A, AC, DC.
- 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
- 耐压值 (Withstanding voltage): 1000V AC/minute.
- 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$.
- 产品料号 (Product material No.):



CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0			

深圳市连盛精密连接器有限公司

OPERATION	DRAW	SCALE	FIT
X.X ± 0.30		UNIT	mm
X.XX ± 0.20	CHECK	SIZE	A4
X.XXX ± 0.10		SHEET	1/1
Angle $\pm 3^{\circ}$	APPROVE	PROJ.	ϕ
DIM TOL			

PART NO.	1130400151
TITLE:	XH-NAW

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
1	2	3	4