









RoHS		2	3	4	5	6	7	8	9																																																							
								序号	品名	材质																																																						
								①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色																																																						
								②	XH2.5直针WTB端子	铜合金/表面镀锡																																																						
																																																																
								带扣打K脚 2PIN																																																								
																																																																
								TYPE 1(无K脚)																																																								
																																																																
								TYPE 2(打K脚)																																																								
																																																																
								SECTION A-A																																																								
																																																																
								常规2 Pin样式																																																								
		技术指标(Technical Index): 1. 温度范围(Temperature range): -25° C~+85° C. 2. 额定电压(Rated voltage): 250V, AC. 3. 额定电流(Rated current): 3.0A AC, DC. 4. 接触电阻(Contact resistance): ≤20mΩ . 5. 耐压值(Withstanding voltage): 1000V AC/minute. 6. 绝缘电阻(Insulation resistance): ≥1000MΩ. 7. 产品料号(Product material No.):																																																														
								适用线路板(PCB LAYOUT)																																																								
								<table><tr><th>CKT</th><th>A</th><th>B</th><th>CKT</th><th>A</th><th>B</th></tr><tr><td>2</td><td>2.5</td><td>7.5</td><td>10</td><td>22.5</td><td>27.5</td></tr><tr><td>3</td><td>5.0</td><td>10.0</td><td>11</td><td>25.0</td><td>30.0</td></tr><tr><td>4</td><td>7.5</td><td>12.5</td><td>12</td><td>27.5</td><td>32.5</td></tr><tr><td>5</td><td>10.0</td><td>15.0</td><td>13</td><td>30.0</td><td>35.0</td></tr><tr><td>6</td><td>12.5</td><td>17.5</td><td>14</td><td>32.5</td><td>37.5</td></tr><tr><td>7</td><td>15.0</td><td>20.0</td><td>15</td><td>35.0</td><td>40.0</td></tr><tr><td>8</td><td>17.5</td><td>22.5</td><td>16</td><td>37.5</td><td>42.5</td></tr><tr><td>9</td><td>20.0</td><td>25.0</td><td></td><td></td><td></td></tr></table>			CKT	A	B	CKT	A	B	2	2.5	7.5	10	22.5	27.5	3	5.0	10.0	11	25.0	30.0	4	7.5	12.5	12	27.5	32.5	5	10.0	15.0	13	30.0	35.0	6	12.5	17.5	14	32.5	37.5	7	15.0	20.0	15	35.0	40.0	8	17.5	22.5	16	37.5	42.5	9	20.0	25.0			
CKT	A	B	CKT	A	B																																																											
2	2.5	7.5	10	22.5	27.5																																																											
3	5.0	10.0	11	25.0	30.0																																																											
4	7.5	12.5	12	27.5	32.5																																																											
5	10.0	15.0	13	30.0	35.0																																																											
6	12.5	17.5	14	32.5	37.5																																																											
7	15.0	20.0	15	35.0	40.0																																																											
8	17.5	22.5	16	37.5	42.5																																																											
9	20.0	25.0																																																														