

RoHS

①

②

③

④

WITH COVER

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.

2. 工作温度: -25° C~85° C.

3. 适用线规: AWG#28~#22.

4. 额定电压: 250V DC/AC(rms).

5. 额定电流: 3.0A.

6. 接触电阻: ≤20mΩ.

7. 耐压值: 1000V AC/minute.

8. 绝缘电阻: ≥1000MΩ.

9. 产品料号:

| CKT | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2   | 2.50  | 7.50  | 10.00 |
| 3   | 5.00  | 10.00 | 12.50 |
| 4   | 7.50  | 12.50 | 15.00 |
| 5   | 10.00 | 15.00 | 17.50 |
| 6   | 12.50 | 17.50 | 20.00 |
| 7   | 15.00 | 20.00 | 22.50 |
| 8   | 17.50 | 22.50 | 25.00 |
| 9   | 20.00 | 25.00 | 27.50 |
| 10  | 22.50 | 27.50 | 30.00 |
| 11  | 25.00 | 30.00 | 32.50 |
| 12  | 27.50 | 32.50 | 35.00 |
| 13  | 30.00 | 35.00 | 37.50 |
| 14  | 32.50 | 37.50 | 40.00 |
| 15  | 35.00 | 40.00 | 42.50 |
| 16  | 37.50 | 42.50 | 45.00 |

2P 结构

| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | OPERATION | DRAW | SCALE | FIT | PART NO. | TITLE: |
|-----|------|--------------------------|--------|-----------|------|-------|-----|----------|--------|
| 1   | 2    | 3                        | 4      | 5         | 6    | 7     | 8   | 9        |        |

RoHS

①

②

③

④

WITH COVER

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.

2. 工作温度: -25° C~85° C.

3. 适用线规: AWG#28~#22.

4. 额定电压: 250V DC/AC(rms).

5. 额定电流: 3.0A.

6. 接触电阻: ≤20mΩ.

7. 耐压值: 1000V AC/minute.

8. 绝缘电阻: ≥1000MΩ.

9. 产品料号:

| CKT | DIM A | DIM B | DIM C |
|-----|-------|-------|-------|
| 2   | 2.50  | 7.50  | 10.00 |
| 3   | 5.00  | 10.00 | 12.50 |
| 4   | 7.50  | 12.50 | 15.00 |
| 5   | 10.00 | 15.00 | 17.50 |
| 6   | 12.50 | 17.50 | 20.00 |
| 7   | 15.00 | 20.00 | 22.50 |
| 8   | 17.50 | 22.50 | 25.00 |
| 9   | 20.00 | 25.00 | 27.50 |
| 10  | 22.50 | 27.50 | 30.00 |
| 11  | 25.00 | 30.00 | 32.50 |
| 12  | 27.50 | 32.50 | 35.00 |
| 13  | 30.00 | 35.00 | 37.50 |
| 14  | 32.50 | 37.50 | 40.00 |
| 15  | 35.00 | 40.00 | 42.50 |
| 16  | 37.50 | 42.50 | 45.00 |

2P 结构

| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | OPERATION | DRAW | SCALE | FIT | PART NO. | TITLE: |
|-----|------|--------------------------|--------|-----------|------|-------|-----|----------|--------|
| 1   | 2    | 3                        | 4      | 5         | 6    | 7     | 8   | 9        |        |