

RoHS		2	3	4	5	6	7	8	9																																																														
								WITH COVER																																																															
								2P 结构																																																															
		技术指标: 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。 2. 工作温度: -25° C~85° C. 3. 适用线规: AWG#28~#22. 4. 额定电压: 250V DC/AC(rms). 5. 额定电流: 3.0A. 6. 接触电阻: ≤20mΩ. 7. 耐压值: 1000V AC/minute. 8. 绝缘电阻: ≥1000MΩ. 9. 产品料号:				<table><thead><tr><th>CKT</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr></thead><tbody><tr><td>2</td><td>2.50</td><td>7.50</td><td>10.00</td></tr><tr><td>3</td><td>5.00</td><td>10.00</td><td>12.50</td></tr><tr><td>4</td><td>7.50</td><td>12.50</td><td>15.00</td></tr><tr><td>5</td><td>10.00</td><td>15.00</td><td>17.50</td></tr><tr><td>6</td><td>12.50</td><td>17.50</td><td>20.00</td></tr><tr><td>7</td><td>15.00</td><td>20.00</td><td>22.50</td></tr><tr><td>8</td><td>17.50</td><td>22.50</td><td>25.00</td></tr><tr><td>9</td><td>20.00</td><td>25.00</td><td>27.50</td></tr><tr><td>10</td><td>22.50</td><td>27.50</td><td>30.00</td></tr><tr><td>11</td><td>25.00</td><td>30.00</td><td>32.50</td></tr><tr><td>12</td><td>27.50</td><td>32.50</td><td>35.00</td></tr><tr><td>13</td><td>30.00</td><td>35.00</td><td>37.50</td></tr><tr><td>14</td><td>32.50</td><td>37.50</td><td>40.00</td></tr><tr><td>15</td><td>35.00</td><td>40.00</td><td>42.50</td></tr><tr><td>16</td><td>37.50</td><td>42.50</td><td>45.00</td></tr></tbody></table>		CKT	DIM A	DIM B	DIM C	2	2.50	7.50	10.00	3	5.00	10.00	12.50	4	7.50	12.50	15.00	5	10.00	15.00	17.50	6	12.50	17.50	20.00	7	15.00	20.00	22.50	8	17.50	22.50	25.00	9	20.00	25.00	27.50	10	22.50	27.50	30.00	11	25.00	30.00	32.50	12	27.50	32.50	35.00	13	30.00	35.00	37.50	14	32.50	37.50	40.00	15	35.00	40.00	42.50	16	37.50	42.50	45.00
CKT	DIM A	DIM B	DIM C																																																																				
2	2.50	7.50	10.00																																																																				
3	5.00	10.00	12.50																																																																				
4	7.50	12.50	15.00																																																																				
5	10.00	15.00	17.50																																																																				
6	12.50	17.50	20.00																																																																				
7	15.00	20.00	22.50																																																																				
8	17.50	22.50	25.00																																																																				
9	20.00	25.00	27.50																																																																				
10	22.50	27.50	30.00																																																																				
11	25.00	30.00	32.50																																																																				
12	27.50	32.50	35.00																																																																				
13	30.00	35.00	37.50																																																																				
14	32.50	37.50	40.00																																																																				
15	35.00	40.00	42.50																																																																				
16	37.50	42.50	45.00																																																																				
		深圳市连盛精密连接器有限公司																																																																					
		深圳																																																																					
		1130400128																																																																					
		XH-NAWV																																																																					
		1																																																																					
		2																																																																					
		3																																																																					
		4																																																																					
		5																																																																					
		6																																																																					
		7																																																																					
		8																																																																					
		9																																																																					

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1130400128
				X.XXX	±0.10					SHEET		
				Angle	±3°	APPROVE					TITLE:	XH-NAWV
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	DIM		TOL			PROJ.		