









PCB.焊接图



H	
6.5	7.0
7.5	8.0
8.5	9.0
9.5	10.0
10.5	11.0
11.5	12.0

TS-1028-ARW

主要技术规格:

- 1.额定值: 50mA DC12V
- 2.接触电阻: $\leq 50m\Omega$
- 3.操作力: $250\pm 40gf$
- 4.行程: $0.35\pm 0.1mm$
- 5.绝缘电阻: $\geq 100M\Omega$
- 6.抗电强度: 250V 50HZ 1Min.
- 7.寿命: 100,000 Cycles
- 8.防水等级: IP67
- 9.防银迁移: 60V, 85℃, 90%RH/60H

弹片:

A: 不锈钢

B: 覆磷铜

定位柱:

R: 无柱

安装方式:

W: 贴片

L: 插件

U: 包脚

F: 沉板

高度:

065: 6.5H

070: 7.0H

.....

115: 11.5H

120: 12.0H

力度:


16: 160g

26: 260g

按键颜色:

B: 黑

R: 红



电路图

序号	零件名称	材料规格	备注
1	按钮	PPA	耐温280℃ (黑色)
2	盖板	PPA	耐温280℃ (黑色)
3	簧片	不锈钢	覆银
4	基座	PPA	耐温280℃ (黑色)
5	引脚、触点	黄铜	镀银
6	防水垫	硅胶	耐温280℃ (黑色)
7	防水膜	PI	耐温280℃ (黑色)
8	内按钮	PPA	耐温280℃ (黑色)

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

>0.5~2: ± 0.10 >2~5: ± 0.25 >5~10: ± 0.30

ANGLES:

 $\pm 0.5^\circ$ TITLE:
TACT SWITCH

PAR TS-1028-ARWXXX-B

DWN

CHKD

APVD

SCALE 1:1 UNIT: MM

SIZE: A4 SHEET: 1F1



REV: A