

RoHS

①

②

③

④

WITH COVER

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.

2. 工作温度: -25° C~85° C.

3. 适用线规: AWG#28~#22.

4. 额定电压: 250V DC/AC(rms).

5. 额定电流: 3.0A.

6. 接触电阻: ≤20mΩ.

7. 耐压值: 1000V AC/minute.

8. 绝缘电阻: ≥1000MΩ.

9. 产品料号:

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00

2P 结构

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	PART NO.	TITLE:
1	2	3	4	5	6	7	8	9	

[illegible][illegible][illegible]