

RoHS		2	3	4	5	6	7	8	9		
									序号	品名	材质
									①	XH2.5直针WTB胶芯	PA66 UL94V-0 米色 白色
									②	XH2.5直针WTB端子	铜合金/表面镀锡
				带扣打K脚 2PIN							
				TYPE 1 (无K脚)		TYPE 2 (打K脚)		SECTION A-A		常规2 Pin样式	
		技术指标 (Technical Index):									
		1. 温度范围 (Temperature range): -25° C~+85° C.									
		2. 额定电压 (Rated voltage): 250V, AC.									
		3. 额定电流 (Rated current): 3.0A AC, DC.									
		4. 接触电阻 (Contact resistance): ≤20mΩ .									
		5. 耐压值 (Withstanding voltage): 1000V AC/minute.									
		6. 绝缘电阻 (Insulation resistance): ≥1000MΩ.									
		7. 产品料号 (Product material No.):									
				适用线路板 (PCB LAYOUT)							