










P.C.B LAYOUT



Main technical performance	
Rated electrical load	DC 24V 3A
Temperature	-30℃~+70℃
Insulation resistance	≥100MΩ
Contact Resistance	≤0.3Ω
Pressure resistance	AC500V(50Hz)/min
Insertion force	3-20N
service life	5000cycles

<i>PIN</i>	<i>P/N</i>
$\varnothing 1.3$	<i>DC050-13T</i>
$\varnothing 2.0$	<i>DC050-20T</i>
$\varnothing 2.5$	<i>DC050-25T</i>

6	圆针	1	黄铜棒	亮锡
5	平片	1	H62黄铜带(Y)T=0.35	亮锡
4	弯片	1	H62黄铜带(Y)T=0.3	亮锡
3	簧片	1	磷铜带T=0.25	亮锡
2	后盖	1	PA9T	黑色
1	底座	1	PA9T	黑色
序号	名称	数量	材料	备注

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.:±0.20	X'.:±1'	PART NO.		TITLE:		
X.X:±0.10	X.X':±0.5'	DC050-NT		DC SOCKET		
X.XX:±0.05		DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			SCALE	SHEET
MATERILA	— — —	APPD: Ava			N:A	1/1