









RoHS

序号	品名	材质
①	HA2.5弯针WTB胶芯	PA66 UL94V-0 米色 白色
②	XH2.5弯针WTB端子	铜合金/表面镀锡



TYPE 2(打K脚)

TYPE 1(无K脚)



SECTION A-A

CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0			

技术指标(Technical Index):

- 温度范围(Temperature range): -25° C~+85° C.
- 额定电压(Rated voltage): 250V, AC.
- 额定电流(Rated current): 3.0A AC, DC.
- 接触电阻(Contact resistance): ≤20mΩ .
- 耐压值(Withstanding voltage): 1000V AC/minute.
- 绝缘电阻(Insulation resistance): ≥1000MΩ.
- 产品料号(Product material No.):

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1130400162
				X.XXX	±0.10				SHEET	1/1		
				Angle	±3°	APPROVE			PROJ.	TITLE:		XHB-NAW
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM							

1 2 3 4 5 6 7 8 9