











RoHS

序号	品名	材质
①	PH2.0直针WTB胶芯	米色 PA66 UL94V-0 白色 红色
②	PH2.0弯针WTB端子	铜合金/表面镀锡



CKT	A	B	CKT	A	B
2	2.0	6.0	12	22.0	26.0
3	4.0	8.0	13	24.0	28.0
4	6.0	10.0	14	26.0	30.0
5	8.0	12.0	15	28.0	32.0
6	10.0	14.0	16	30.0	34.0
7	12.0	16.0	17	32.0	36.0
8	14.0	18.0	18	34.0	38.0
9	16.0	20.0	19	36.0	40.0
10	18.0	22.0	20	38.0	42.0
11	20.0	24.0			

- 技术指标(Technical Index):
1. 工作温度(Temperature range): -40° C~85° C.
 2. 额定电压(Rated voltage): 250V DC/AC(rms).
 3. 额定电流(Rated current): 2.0A.
 4. 接触电阻(Contact resistance): ≤25mΩ.
 5. 耐压值(Withstanding voltage): 500V AC/minute.
 6. 绝缘电阻(Insulation resistance): ≥1000MΩ.
 7. 产品料号(Product material No.):



REV		DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
1		2	3	4	X.X		±0.30	UNIT	mm		
					X.XX		±0.20	SIZE	A4		
					X.XXX		±0.10	SHEET	1/1		
					Angle		±3°	PROJ.	1/1	PART NO.	1130300174
					DIM		TOL			TITLE:	PH-NAW