









REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




PIN	P/N
ø2.0	DC-007B-20
ø2.5	DC-007B-25




PCB.WELDING DRAWING (TOLERANCE:±0.05)

Main technical performance	
Rated electrical load	DC 24V 8A
Contact resistance	≤0.03Ω
Insulation resistance	≥100MΩ DC250V
Pressure resistance	AC 500V 1min
Insertion force	3-30N
Operating temperature range	-40℃~+85℃
service life	5000cycles



RECOMMEND PULG



SCHEMATIC

5	圓針	1	黃銅棒	鍍銀
4	蓋片	1	H62黃銅帶(Y)	鍍銀
3	簧片	1	磷銅帶	銅錫
2	屏蔽罩	1	H62黃銅帶(Y)	黑
1	基座	1	PPA	黑
序号	名称	数量	材料	备注

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X'.:±5°	PART NO. DC-007B-N		TITLE: DC SOCKET	
X.X:±0.25	X.X':±1°				
X.XX:±0.15					
UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1