




NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC,POLYESTER(94V-0),COLOR:BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
2. FINISH(CONTACT AREA): 0.38μm PdNi & Au PLATING OVER NICKEL
3. FINISH(CONTACT AREA): 0.76μm PdNi & Au PLATING OVER NICKEL
4. FINISH(CONTACT AREA): 2.0 μmMIN TIN PLATED OVER NICKEL
5. FINISH(RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL
6. FINISH(RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

A ROW		X	Y		3-917657-5
B ROW					3-917657-3
A ROW		Y	Y		2-917657-5
B ROW					2-917657-3
A ROW		X	X		1-917657-5
B ROW					1-917657-3
					1-917657-2

KEYING LOCATION	A ROW KEYING	B ROW KEYING	FINISH	製品番号	PART NO.
TE Connectivity					
WIRE RANGE	INSULATION DIA	NAME ダイナミック D-3200 垂直タイプ 10 極 ヘッダーアセンブリー			
MATERIAL SEE NOTE 注記参照	FINISH SEE NOTE 注記参照	DYNAMIC D-3200 10 POS.V-HDR ASS'Y			
DR. 24/APR/'95 K.IKEDA	DE. 24/APR/'95 K.IKEDA	一般公差 (GENERAL TOLERANCE)			
CHK. 24/APR/'95 S.MANABE	APP. 24/APR/'95 S.MANABE	10mm ±0.3 10mm 3mm ±0.4 30mm 100mm ±0.45 角 度 ±3°			
C REVISED PER ECR-25-250788 F.Z R.B 16JAN 2025		B1 REVISED PER ECO-11-005030 RK HMR 26MAR11		LTR REVISION RECORD DR CHK DATE	
SCALE 2-1		REV. C		SHEET 1 OF 1	