








Typical Specifications

1. Rating : 12V 0.3A DC
2. Insulation Resistance: 100M min
3. Operating Life : 10,000 cycles



Schematic(Shorting)



P.C.B layout

⑤	Knob	—	1	POM	Black	—
④	Contact Clip	—	1	C5210	Ag Clad	—
③	Cover	—	1	SUS	Natural	—
②	Base	—	1	PCB	—	—
①	Terminal	—	3	Brass	Ag Plated	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE				
DRAWN	JKUN.LU	2021.4.16				
CHECKED				TITLE:	SLIDE SWITCHS	
APPROVALS				PART NO.	SS-12D02-VG4	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10				
			±2°	DRAWING NO.	_____	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			