




PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldering temperature:255±5℃, 10S

波峰焊温度: 255±5℃, 10S

X4611 W V - 02 I - C40 D28  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~40P
- 5.Plastic Height:l=2.0mm
- 6.Pin Length:C=4.0mm
- 7.Pin Length:D=2.8mm

|                    |          |               |                        |
|--------------------|----------|---------------|------------------------|
| X4611WV-02I-C40D28 | PA6T     | Brass         | X4611F                 |
| PART NO            | Material | Material(Pin) | Suitable XKB<br>Female |

|                                                   |             |      |         |          |                        |      |
|---------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                   |             |      |         |          | ANGLAR                 | ±5°  |
| ΔX                                                |             |      |         |          | L≤ 4                   | ±0.2 |
| ΔX                                                |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                                |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                              | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                         |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |             |      |         |          |                        |      |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|                         |  |                                                                                             |                                    |       |          |
|-------------------------|--|---------------------------------------------------------------------------------------------|------------------------------------|-------|----------|
| DSND                    |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.0mm BTB Connector |       |          |
| DWN                     |  | VIEW:  | PART NO.:<br>X4611WV-02I-C40D28    |       |          |
| CHKD                    |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X4611WV-02I-C40D28   |       |          |
| APPD                    |  | SIZE: A4                                                                                    |                                    |       |          |
| L PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                             | SHEET | REVISION |
|                         |  |                                                                                             |                                    | 1/1   | A0       |