










序号	品名	材质
1	0.5后翻胶芯(H2.0)	LCP UL94V-0 本色
2	0.5后翻端子(H2.0)	铜合金/表面点镀金
3	0.5后翻后盖(H2.0)	LCP UL94V-0 黑色
4	0.5后翻焊片(H2.0)	铜合金/表面镀锡

适用扁平线(Applicable Flat Cable)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。

Part No	Pin	A	B	C
FPC-0.5HF-4PWBR-H20	4	1.50	2.52	5.54
FPC-0.5HF-5PWBR-H20	5	2.00	3.02	6.04
FPC-0.5HF-6PWBR-H20	6	2.50	3.52	6.54
FPC-0.5HF-7PWBR-H20	7	3.00	4.02	7.04
FPC-0.5HF-8PWBR-H20	8	3.50	4.52	7.54
FPC-0.5HF-9PWBR-H20	9	4.00	5.02	8.04
FPC-0.5HF-10PWBR-H20	10	4.50	5.52	8.54
FPC-0.5HF-11PWBR-H20	11	5.00	6.02	9.04
FPC-0.5HF-12PWBR-H20	12	5.50	6.52	9.54
.....				
FPC-0.5HF-60PWBR-H20	60	(60-1)*0.5	(60+1)*0.5+0.02	(60+7)*0.5+0.04
FPC-0.5HF-80PWBR-H20	80	(80-1)*0.5	(80+1)*0.5+0.02	(80+7)*0.5+0.04

适用线路板(PCB LAYOUT)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 0.5 Pitch H2.0 Backflip R/A Type CONN
DECIMALS:	ANGLES:		PAR FPC-0.5HF-NPWBR-H20
.X:±0.30	.X':±5°		DWN
.XX:±0.20	.XX':±2°		CHKD
.XXX:±0.05	.XXX':±1°		APVD
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A