

RoHS&REACH







REV.	DESCRIPTION	DATE
A	NEW	2025.09.23

材料Material:

- 外壳材质: PBT,PA46 (UL 94V-0)
Housing Material: PBT,PA46 (UL 94V-0)
- 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;Gold Plating Over Nickel

电气Electrical:

- 额定电压: 125伏
Voltage Rating : 125 V Rms
- 额定电流: 1.5安培
Current Rating: 1.5 AMP
- 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX
- 绝缘电阻: 500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V
- 绝缘耐压: 50-60Hz 1000V AC, 1分钟
DIELECTRIC STRENGTH:1000V AC 50Hzor 60Hz, 1MIN.
- 耐久: 插拔750次以上
Durability: 750 Cycles Min
- 工作温度: -40℃ ~+85℃
Operation Temperature: -40℃ ~+85℃



Positions	Contacts	Ports	Plastic	Color	Gold Plating
6/8	2/4/6/8	1-1x1 2-1x2 3-1x3 4-1x4 5-1x5 n-1xn	1-PBT 2-PA46 3-Other	1-Black 2-Gray 3-Other	1-G/Fu" 2-1u" 3-3u" 4-6u" 5-15u" 6-30u" 7-Other

DRAWN BY: FANG	TOLERANCE UNSPECIFIED	SIZE: 1:1		恒连电子科技有限公司 EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD	
CHECKED BY: FANG	X. ±0.5 ±2.0° .X ±0.38 ±1.5° .XX ±0.25 ±1.0° XXX ±0.15 ±0.5°	UNIT: mm SIZE: A4 REV: A			
APPROVED BY: DING	PROJECTION	SHEET 1 OF 1	TITLE: 5303 1x1 6P6C	DWG NO: 5303-660XXX	http://www.chinarj45.com
			PART NO: N/A	No:	N/A