




RoHS&REACH

REV.	DESCRIPTION	DATE
A	NEW	2025.1.2

材料Material:

1. 外壳材质: PBT,PA46 (UL 94V-0)
Housing Material: PBT,PA46 (UL 94V-0)
2. 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter
Phosphor Bronze;Gold Plating Over Nickel

电气Electrical:

1. 额定电压: 125伏
Voltage Rating : 125 V Rms
2. 额定电流: 1.5安培
Current Rating: 1.5 AMP
3. 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms MaX
4. 绝缘电阻: 500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V
5. 绝缘耐压: 50-60Hz 1000V AC, 1分钟
DIELECTRIC STRENGTH:1000V AC 50Hzor 60Hz, 1MIN.
6. 耐久: 插拔750次以上
Durability: 750 Cycles Min
7. 工作温度: -40℃ ~+85℃
Operation Temperature: -40℃ ~+85℃

Positions	Contacts	Ports	Panel	Plastic	Color	Gold Plating
6	2, 4 or 6	1-1x2 2-1x3 3-1x4 4-1x5 5-1x6	0-w/O panel 1-w/ Panel	1-PBT 2-PA46 3-Other	1-Black 2-Gary 3-Other	1-G/Fu" 2-1u" 3-3u" 4-6u" 5-15u" 6-Other

PC Board Layout
Component Side Shown

DRAWN BY: FANG	TOLERANCE UNSPECIFIED	SIZE	1:1		恒连电子科技有限公司 EVERCOM ELECTRONIC TECHNOLOGY CO.,LTD	
CHECKED BY: FANG	X. ±0.50 ±2.0"	UNIT: mm				
APPROVED BY: DING	.X ±0.38 ±1.5"	SIZE: A4				
PROJECTION	.XX ±0.25 ±1.0"	REV. A	TITLE: 5503 1x6 6P6C 有边缺口			
	.XXX ±0.15 ±0.5"	REV. A		PART NO: 5503-6651XXX	http://www.chinarj45.com	